



PROTECTION



COMFORT



FIT

ANGA 4310 FFP3 NR D



CHARACTERISTICS

- Folding model and therefore easy to store
- Easy-to-shape noseband
- Equipped with exhalation valve
- The head straps ensure that the mask stays firmly in place and provide a good seal
- Latex-free head straps
- Individually wrapped
- This mask is not reusable
- This mask has passed the Dolomite dust test
- Packed per 20 pieces in a nice, handy dispenser box
- Can be used against dust particles up to 50x the limit value

Article number: 4.05.431.00

SUITABLE FOR ACTIVITIES IN E.G.

- Construction
- Industry
- Transport & Logistics
- Shipbuilding
- Metalworking
- Pharmaceutical

COLOUR

White


PACKAGING

- 20 pieces in a dispenser box
- 240 pieces (12x20) in a case


CE 2797
EN 149:2001+A1:2009

PRODUCT INFORMATION

SIZE	ARTICLE NO.	EAN CODE 20 PIECES (DISPENSER BOX)	EAN CODE 240 PIECES 12X20 (CASE)
one size	4.05.431.00	8718249020803	8718249020810



WEARING INSTRUCTIONS



1. Place your fingers in the mask, bending the noseband around the fingers to form the contours of the nose. **2.** Hold the mask with one hand in position over the nose and mouth, with the head straps around the outside of the hand. Pull the lower part of the elastic band over the head and place it on the neck (under the ears). **3.** Stretch the upper part of the elastic band and place it over the crown of the head (just above the ears). **4.** With both hands, press the nose clip and shape it around your nose. Adjust the tension in the upper and lower part of the continuous head strap so that the mask fits well on the face. **5.** Fold both hands over the mask and take a deep breath. Negative pressure should now be noted in the mask. If air leaks around the nose, the nosepiece should be made tighter. If air leaks along the sides, adjust the head straps. ***NOTE:** Replace the mask immediately if breathing is impeded or if the mask is twisted or damaged. Also do this if a good fit on the face cannot or can no longer be achieved.

STORAGE REQUIREMENTS

The dust masks are for single use (maximum 1 shift). No maintenance required. After single use, discard the mask in accordance with local regulations. The masks should be kept out of direct sunlight in their packaging until used.

TESTING INSTITUTE

This dust mask is certified by: BSI Group The Netherlands BV (Notify Body no. 2797), John M. Keynesplein 9, 1066 EP Amsterdam, The Netherlands.

DECLARATION OF CONFORMITY

For a copy of the declaration of conformity, please refer to the following web link: www.oxxa-safety.com/doc

RELATED ITEMS



TAIVAS 6340
ART. NO. 4.05.634.00

YOUR SUPPLIER: